



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Coax	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.00 - 5.10 mm
Size	0A

https://www.lemo.com/int_en/ffa-0a-250-ntac52z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax	Solder
Insert configuration value	0A.250 - 1 Coax (50 Ohm)
OHM	50
Contact Type	Coaxial 50 Ohm (Solder)
Bucket Dia.	1.1

Form & Material

Shell style / Model id	FFA - Straight plug with cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Push-pull
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	7.85 g

Environment

Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Salt Spray Corrosion	>144 hr

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	4.00 - 5.10 mm

https://www.lemo.com/int_en/ffa-0a-250-ntac52z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Drawings



Dimensions

	A	B	S1	S2	L	M
mm.	9	9	7.5	7	37	27.5
in.	0.35	0.35	0.3	0.28	1.46	1.08

Cables

Cable PartNumber	Material	Colour	Cable image
158480	PUR	Black	
158490	PVC	Black	
CCX.50.088.292495N	PVC	Black	
CCX.50.RG5.8CU50N	PVC	Black	

https://www.lemo.com/int_en/ffa-0a-250-ntac52z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.