



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts High Voltage	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	2.70 - 3.60 mm
Size	1Y
Suggested matching part	<a href="#">ERA.1Y.405.CLA</a>
Series	Y - High Voltage Unipole

[https://www.lemo.com/int\\_en/solutions/supreme/y-high-voltage-unipole/ffa-1y-405-cllc37.html](https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffa-1y-405-cllc37.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts High Voltage	1
Contact Termination High voltage	Solder
Insert configuration value	1Y.405 - 1 High Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	8 A
Test voltage (kV DC)	10.5
Creepage distance	16 mm

## Form & Material

Shell style / Model id	FFA - Straight plug with cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular
Colour	Grey
Weight	34.88 g

## Environment

Technical domain	Specialties and Other
Environmental sealing (IP rating)	IP50
Salt Spray Corrosion	>1000 hr



## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	2.70 - 3.60 mm

# Drawings

[https://www.lemo.com/int\\_en/solutions/supreme/y-high-voltage-unipole/ffa-1y-405-cllc37.html](https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffa-1y-405-cllc37.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Dimensions

	A	L	M	S1
mm.	13	67	30.5	9
in.	0.51	2.64	1.2	0.35