



Summary

[Request a quote](#)

[Catalog](#)

High Voltage	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.20 - 5.20 mm
Size	1Y
Matching parts	ERA.1Y.410.CTL
Series	Y - High Voltage Unipole

Technical details

Electrical Configuration

Contact Termination High voltage	Solder
Insert configuration value	1Y.410 - 1 High Voltage
Insulator	T: PTFE
Rated current	8 Amps
Test voltage (kV AC)	10.5
Contact Type	Solder
Creepage distance	24.5 mm
High Voltage	1

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffa-1y-410-ctac52.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

Shell style / Model id	FFA - Straight plug with cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular
Weight	36.05 g

Environment

Technical domain	Specialties and Other
Environmental protection (IP rating)	IP50
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	4.20 - 5.20 mm

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffa-1y-410-ctac52.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.