



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	4
Wire Size/AWG	20 - 12
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	9.60 - 10.50 mm
Size	4E
Suggested matching part	<a href="#">ERA.4E.304.CLL</a>
Series	E - Outdoor Stepped Insert

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/ffa-4e-304-clac10.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-4e-304-clac10.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	4
Contact Termination Low voltage	Solder
Insert configuration value	4E.304 - 4 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	22 A
Test voltage (kV DC)	3
Bucket Dia.	2.7
Contact Dia.	3
Wire Size/AWG	20 - 12

## Form & Material

Shell style / Model id	FFA - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with male pin 1
Colour	Grey
Weight	148.21 g

## Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/ffa-4e-304-clac10.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-4e-304-clac10.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	9.60 - 10.50 mm

# Recommended By Lemo

## Accessories

Compatible cap	<a href="#">BFA.4E.100.NAS</a>
----------------	--------------------------------

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/ffa-4e-304-clac10.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-4e-304-clac10.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.