



## Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.10 - 4.70 mm
Size	0A

## Technical details

### Electrical Configuration

Coax	1
Contact Termination Coax	Solder
Insert configuration value	0A.275 - 1 Coax (75 Ohm)
Contact Type	Coaxial 75 Ohm (Solder)
Bucket Dia.	0.65

[https://www.lemo.com/int\\_en/ffs-0a-275-ntae48.html](https://www.lemo.com/int_en/ffs-0a-275-ntae48.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Form & Material

Shell style / Model id	FFS - Straight plug , cable crimping
Plug	Straight
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Push-pull
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	6.76 g


## Environment

Environmental protection (IP rating)	IP50
Salt Spray Corrosion	>144 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Crimp
Jacket cable outside diameter [mm]	4.10 - 4.70 mm

## Drawings



## Dimensions

	<b>A</b>	<b>L</b>	<b>M</b>	<b>S2</b>	<b>S1</b>
mm.	9	37	28	7.5	7.5
in.	0.35	1.46	1.1	0.3	0.3

[https://www.lemo.com/int\\_en/ffs-0a-275-ntae48.html](https://www.lemo.com/int_en/ffs-0a-275-ntae48.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.