

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

[BKT series](#)

| | |
|------------------------------------|--------------------------------|
| Nb of contacts Coax | 1 |
| Gender | Standard |
| Plug | Plug - Straight |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 2.10 - 2.50 mm |
| Size | 1K |
| Suggested matching part | EGA.1K.250.CTL |
| Series | K - Outdoor keyed |

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fga-1k-250-ctac25z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---|--------------------------|
| Nb of contacts Coax | 1 |
| Contact Termination Coax - Conductor fixing | Solder |
| Insert configuration value | 1K.250 - 1 Coax (50 Ohm) |
| Insulator | T: PTFE |
| Impedance | 50 Ohms |
| Gender | Standard |

Form & Material

| | |
|------------------------|--|
| Shell style / Model id | FG - Straight plug, cable collet and nut for fitting a bend relief |
| Plug | Straight |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces |
| Locking system | Push-pull |
| Keying | 2 keys (alpha=30, plug: male contacts, receptacle: female contacts) |
| Colour | Grey |
| Variant | Nut for fitting a bend relief |
| Weight | 24.86 g |

Environment

| | |
|-----------------------------------|---|
| Technical domain | Audio Video, Energy and Industrial, Medical, Test and Measurement |
| Environmental sealing (IP rating) | IP68 |
| Endurance | 5000 mating cycles |
| Temperature range | -55°C / +200°C (max. temperature valid for short periods of use.) |
| Climatic Category | 50/175/21 |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Shielding (min) | 95 dB (10 MHz) |
| Shielding (min) | 80 dB (1 GHz) |
| Shock Resistance | 100 g [6 ms] |
| Vibration | 15 g [10 Hz - 2000 Hz] |
| Salt Spray Corrosion | >1000 hr |


https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fga-1k-250-ctac25z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

| | |
|------------------------------------|-----------------------|
| Cable termination protection | For cable bend relief |
| Fixation type | Cable collet |
| Jacket cable outside diameter [mm] | 2.10 - 2.50 mm |

Drawings



Dimensions

| | M | A | S2 | L |
|-----|----------|----------|-----------|----------|
| mm. | 28 | 13 | 9 | 42 |
| in. | 1.1 | 0.51 | 0.35 | 1.65 |

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fga-1k-250-ctac25z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.