



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

[See video assembly instructions](#)

|                                    |                                |
|------------------------------------|--------------------------------|
| Number of contacts Low Voltage     | 4                              |
| Wire Size/AWG                      | 28 - 20                        |
| Gender                             | Standard                       |
| Plug                               | Plug - Straight                |
| Locking system                     | Push-pull                      |
| Jacket cable outside diameter [mm] | 4.30 - 5.20 mm                 |
| Size                               | 2B                             |
| Suggested matching part            | <a href="#">EGB.2B.304.CLL</a> |
| Series                             | B - Indoor keyed               |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgb-2b-304-clad52.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgb-2b-304-clad52.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

|                                 |                              |
|---------------------------------|------------------------------|
| Number of contacts Low Voltage  | 4                            |
| Contact Termination Low voltage | Solder                       |
| R (max)                         | 3.6 mOhm                     |
| Insert configuration value      | 2B.304 - 4 Low Voltage       |
| Insulator                       | L: PEEK (UL 94 / V-0/1.5)    |
| Rated current                   | 15 A                         |
| Vtest (contact-contact)         | 2.6 kV (DC)                  |
| Vtest (contact-shell)           | 2.6 kV (DC)                  |
| Max. Solid Conductor            | 0.5 mm <sup>2</sup> (AWG 20) |
| Max. Stranded Conductor         | 0.5 mm <sup>2</sup> (AWG 20) |
| Bucket Dia.                     | 1 mm (0.039in)               |
| Contact Dia.                    | 1.3 mm (0.051in)             |
| Wire Size/AWG                   | 28 - 20                      |
| Gender                          | Standard                     |

## Form & Material

|                        |   |
|------------------------|---|
| Shell style / Model id | FG - Straight plug, cable collet  |
| Plug                   | Straight  |
| Housing material       | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system         | Push-pull   |
| Keying                 | B: 2 keys (alpha=45, plug: male contacts, receptacle: female contacts)  |
| Colour                 | Grey  |
| Weight                 | 29.04 g   |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgb-2b-304-clad52.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgb-2b-304-clad52.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

|                                   |  |
|-----------------------------------|--|
| Technical domain                  | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50   |
| Endurance                         | 5000 mating cycles   |
| Temperature range                 | -55°C / +250°C (max. temperature valid for short periods of use.)  |
| Climatical Category               | 50/175/21  |
| Humidity (max)                    | <=95% [at 60 deg C /140 F]   |
| Shielding (min)                   | 75 dB (10 MHz)   |
| Shielding (min)                   | 40 dB (1 GHz)  |
| Shock Resistance                  | 100 g [ 6 ms]  |
| Vibration                         | 15 g [10 Hz - 2000 Hz]   |
| Salt Spray Corrosion              | >1000 hr   |







## Cable fixation

|                                    |  |
|------------------------------------|--|
| Cable termination protection       | Standard back nut (no additional protection) |
| Fixation type                      | Cable collet                                 |
| Jacket cable outside diameter [mm] | 4.30 - 5.20 mm                               |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgb-2b-304-clad52.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgb-2b-304-clad52.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Cables

| Cable PartNumber   | Material      | Colour | Cable image   |
|--------------------|---------------|--------|---|
| CMN.04.T22.047QGC  | TPR           | Grey   |   |
| CMN.04.T22.048QGZE | TPR (medical) | Grey   |  |
| 140240             | PVC           | Black  |  |
| 140250             | PVC           | Grey   |  |
| 40260              | PVC           | Black  |  |
| 4080               | PVC           | Grey   |   |
| 4221               | PVC           | Black  |  |
| 4280               | PVC           | Black  |  |
| 80080              | PVC           | Grey   |   |
| 80082              | PVC           | Red    |   |
| 80084              | PVC           | Black  |   |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgb-2b-304-clad52.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgb-2b-304-clad52.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.