



Image for illustrative purpose only

Summary

Request a quote	
Catalog	
Number of contacts Low Voltage	1
Wire Size/AWG	32 - 28
Size	00
Suggested matching part	EGG.00.654.ZZM

Technical details

Electrical Configuration

Number of contacts Low Voltage	1
Contact Termination Low voltage	Crimp
Contact Dia.	0.5
Wire Size/AWG	32 - 28

Form & Material

Shell style / Model id	FG - Male crimp contact, standard barrel
Housing material	Gold plated [ISO 27874] brass
Keying	No keying
Weight	0.04 g

Environment

Environmental sealing (IP rating)	No IP rating
-----------------------------------	--------------

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

Recommended By Lemo

Tools

Positionner	DCE.91.050.0VC
Crimp tool	DPC.91.701.V

https://www.lemo.com/int_en/fgg-00-554-zzc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.