



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Locking system	Push-pull
Jacket cable outside diameter [mm]	2.80 - 3.50 mm
Size	00

[https://www.lemo.com/int\\_en/fgg-00-735-dn.html](https://www.lemo.com/int_en/fgg-00-735-dn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Form & Material

Shell style / Model id	FG - 00 series cable collet
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) collet
Locking system	Push-pull
Keying	No keying
Weight	0.33 g

## Environment

Environmental sealing (IP rating)	IP50
-----------------------------------	------

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Jacket cable outside diameter [mm]	2.80 - 3.50 mm

[https://www.lemo.com/int\\_en/fgg-00-735-dn.html](https://www.lemo.com/int_en/fgg-00-735-dn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.