



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

[See video assembly instructions](#)

|                                    |                                |
|------------------------------------|--------------------------------|
| Number of contacts Low Voltage     | 14                             |
| Wire Size/AWG                      | 34 - 28                        |
| Gender                             | Standard                       |
| Plug                               | Plug - Straight                |
| Locking system                     | Push-pull                      |
| Jacket cable outside diameter [mm] | 4.30 - 5.20 mm                 |
| Size                               | 1B                             |
| Suggested matching part            | <a href="#">EGG.1B.314.CLL</a> |
| Series                             | B - Indoor keyed               |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-1b-314-clad52.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-1b-314-clad52.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

|                                 |                               |
|---------------------------------|-------------------------------|
| Number of contacts Low Voltage  | 14                            |
| Contact Termination Low voltage | Solder                        |
| R (max)                         | 8.7 mOhm                      |
| Insert configuration value      | 1B.314 - 14 Low Voltage       |
| Insulator                       | L: PEEK (UL 94 / V-0/1.5)     |
| Rated current                   | 2 A                           |
| Vtest (contact-contact)         | 1.1 kV (DC)                   |
| Vtest (contact-shell)           | 1.7 kV (DC)                   |
| Max. Solid Conductor            | 0.09 mm <sup>2</sup> (AWG 28) |
| Max. Stranded Conductor         | 0.09 mm <sup>2</sup> (AWG 28) |
| Bucket Dia.                     | 0.45 mm (0.018in)             |
| Contact Dia.                    | 0.5 mm (0.02in)               |
| Wire Size/AWG                   | 34 - 28                       |
| Gender                          | Standard                      |

## Form & Material

|                        |   |
|------------------------|---|
| Shell style / Model id | FG - Straight plug, cable collet  |
| Plug                   | Straight  |
| Housing material       | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system         | Push-pull   |
| Keying                 | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)  |
| Colour                 | Grey  |
| Weight                 | 16.47 g   |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-1b-314-clad52.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-1b-314-clad52.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

|                                   |  |
|-----------------------------------|--|
| Technical domain                  | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50   |
| Endurance                         | 5000 mating cycles   |
| Temperature range                 | -55°C / +250°C (max. temperature valid for short periods of use.)  |
| Climatical Category               | 50/175/21  |
| Humidity (max)                    | <=95% [at 60 deg C /140 F]   |
| Shielding (min)                   | 75 dB (10 MHz)   |
| Shielding (min)                   | 40 dB (1 GHz)  |
| Shock Resistance                  | 100 g [ 6 ms]  |
| Vibration                         | 15 g [10 Hz - 2000 Hz]   |
| Salt Spray Corrosion              | >1000 hr   |

## Cable fixation

|                                    |  |
|------------------------------------|--|
| Cable termination protection       | Standard back nut (no additional protection) |
| Fixation type                      | Cable collet                                 |
| Jacket cable outside diameter [mm] | 4.30 - 5.20 mm                               |

# Recommended By Lemo

## Accessories

|                |                                 |
|----------------|---------------------------------|
| Compatible cap | <a href="#">BFG.1B.100.PCZG</a> |
|----------------|---------------------------------|

## Tools

|                |                                  |
|----------------|----------------------------------|
| Spanner        | <a href="#">DCP.91.001.TN</a>    |
| Spanner wrench | <a href="#">DCD.1B.ZZZ.PA090</a> |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-1b-314-clad52.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-1b-314-clad52.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.