



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Thermocouple	1
Wire Size/AWG	20 - 18
Plug	Plug - Straight
Size	1B
Series	B - Indoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-1b-565-zzk.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-1b-565-zzk.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Thermocouple	1
Wire Size/AWG	20 - 18

## Form & Material

Shell style / Model id	FG - Type K thermocouple male crimp contact, standard barrel
Plug	Straight
Housing material	Thermocouple / Chromel
Keying	No keying
Weight	0.25 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	No IP rating
Temperature range	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-1b-565-zzk.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-1b-565-zzk.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.