



## Summary

[Request a quote](#)

[Catalog](#)

[See video assembly instructions](#)

|                                    |                                |
|------------------------------------|--------------------------------|
| Number of contacts Low Voltage     | 4                              |
| Wire Size/AWG                      | 28 - 20                        |
| Gender                             | Standard                       |
| Plug                               | Plug - Straight                |
| Locking system                     | Push-pull                      |
| Jacket cable outside diameter [mm] | 6.30 - 7.20 mm                 |
| Size                               | 2B                             |
| Matching parts                     | <a href="#">EGG.2B.304.CLL</a> |
| Series                             | B - Indoor keyed               |

## Technical details

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-2b-304-clad72z.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-2b-304-clad72z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

|                                 |                              |
|---------------------------------|------------------------------|
| Contact Termination Low voltage | Solder                       |
| R (max)                         | 3.6 mOhm                     |
| Insert configuration value      | 2B.304 - 4 Low Voltage       |
| Insulator                       | L: PEEK (UL 94 / V-0/1.5)    |
| Rated current                   | 15 Amps                      |
| Vtest (contact-contact)         | 1850 V (AC), 2600 V (DC)     |
| Vtest (contact-shell)           | 1850 V (AC), 2600 V (DC)     |
| Contact Type                    | Solder                       |
| Max. Solid Conductor            | 0.5 mm <sup>2</sup> (AWG 20) |
| Max. Stranded Conductor         | 0.5 mm <sup>2</sup> (AWG 20) |
| Bucket Dia.                     | 1 mm (0.039in)               |
| Contact Dia.                    | 1.3 mm (0.051in)             |
| Number of contacts Low Voltage  | 4                            |
| Wire Size/AWG                   | 28 - 20                      |
| Gender                          | Standard                     |

## Form & Material

|                        |   |
|------------------------|---|
| Shell style / Model id | FG - Straight plug, cable collet and nut for fitting a bend relief  |
| Plug                   | Straight  |
| Housing material       | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system         | Push-pull   |
| Keying                 | 1 key (alpha=0, plug: male contacts, receptacle: female contacts)   |
| Variant                | Nut for fitting a bend relief   |
| Weight                 | 29.6 g  |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-2b-304-clad72z.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-2b-304-clad72z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

|                                      |  |
|--------------------------------------|--|
| Technical domain                     | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental protection (IP rating) | IP50   |
| Minimal temperature                  | -55°C / +250°C   |
| Climatical Category                  | 50/175/21  |
| Humidity (max)                       | <=95% [at 60 deg C /140 F]   |
| Shielding (min)                      | 75 dB (10 MHz)   |
| Shielding (min)                      | 40 dB (1 GHz)  |
| Shock Resistance                     | 100 g [ 6 ms]  |
| Vibration                            | 15 g [10 Hz - 2000 Hz]   |
| Salt Spray Corrosion                 | >1000 hr   |

## Cable fixation

|                                    |                       |
|------------------------------------|-----------------------|
| Cable termination protection       | For cable bend relief |
| Fixation type                      | Cable collet          |
| Jacket cable outside diameter [mm] | 6.30 - 7.20 mm        |

# Recommended By Lemo

## Accessories

|                |                                 |
|----------------|---------------------------------|
| Compatible cap | <a href="#">BFG.2B.100.PCSG</a> |
|----------------|---------------------------------|




## Tools

|                |                                  |
|----------------|----------------------------------|
| Spanner        | <a href="#">DCP.91.023.TN</a>    |
| Spanner wrench | <a href="#">DCD.2B.ZZZ.PA120</a> |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-2b-304-clad72z.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-2b-304-clad72z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Cables

| Cable PartNumber   | Material | Colour | Cable image   |
|--------------------|----------|--------|---|
| 240750             | PVC      | Grey   |  |
| 417920             | PVC      | Grey   |  |
| CTR.75.030.121870G | PVC      | Grey   |  |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-2b-304-clad72z.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-2b-304-clad72z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.