



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|------------------|
| Gender | Standard |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 5.30 - 6.20 mm |
| Size | 2B |
| Series | B - Indoor keyed |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-2b-762-dn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|--------|----------|
| Gender | Standard |
|--------|----------|

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | FG - B series cable collet |
| Housing material | Brass (nickel plated [SAE AMS QQ N 290]) collet |
| Locking system | Push-pull |
| Keying | No keying |
| Weight | 4.35 g |

Environment

| | |
|-----------------------------------|--|
| Technical domain | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50 |
| Endurance | 5000 mating cycles |
| Temperature range | -55°C / +250°C |
| Climatical Category | 50/175/21 |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Shielding (min) | 75 dB (10 MHz) |
| Shielding (min) | 40 dB (1 GHz) |
| Shock Resistance | 100 g [6 ms] |
| Vibration | 15 g [10 Hz - 2000 Hz] |

Cable fixation

| | |
|------------------------------------|--|
| Cable termination protection | Standard back nut (no additional protection) |
| Jacket cable outside diameter [mm] | 5.30 - 6.20 mm |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-2b-762-dn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.