



## Summary

[Request a quote](#)

[Catalog](#)

Coax	3
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	8.10 - 8.50 mm
Size	2K
Matching parts	<a href="#">EGG.2K.243.CLL2</a>
Series	K - Outdoor keyed

## Technical details

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-2k-243-clac852.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-2k-243-clac852.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Coax	3
Contact Termination Coax	Solder
Insert configuration value	2K.243 - 3 Coax (50 Ohm)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Coax contact resistance	<6mOhms
Contact Type	Coaxial 50 Ohm (Solder) Type E
Shell elec. Continuity	<2 mOhms
Cable type	Cable type: A RG 178 B/U, RG 196 A/U S
Gender	Standard

## Form & Material

Shell style / Model id	FG - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Weight	43.08 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental protection (IP rating)	IP68
Minimal temperature	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr


[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-2k-243-clac852.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-2k-243-clac852.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	8.10 - 8.50 mm

## Drawings



## Dimensions

	<b>A</b>	<b>L</b>	<b>M</b>	<b>S 2</b>
mm.	16	52	36	12
in.	0.63	2.05	1.42	0.47

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-2k-243-clac852.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-2k-243-clac852.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.