



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Coax	2
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Size	3K
Suggested matching part	<a href="#">EGG.3K.242.CLM1</a>
Series	K - Outdoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-3k-242-clcc53z.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-3k-242-clcc53z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Coax	2
Contact Termination Coax - Conductor fixing	Crimp
Contact Termination Coax - Screen fixing	Crimp
R (max)	5.8 mOhm
Insert configuration value	3K.242 - 2 Coax (50 Ohm)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	2 A
Impedance	50 Ohm
Vtest	1500 V (AC), 2100 V (DC)
Max. Conductor	0.34 mm <sup>2</sup> (AWG 22)
Min. Conductor	0.34 mm <sup>2</sup> (AWG 22)
Contact Dia.	0.7 mm (0.028in)
Gender	Standard

## Form & Material

Shell style / Model id	FG - Straight plug, cable adapter and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	71.64 g

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-3k-242-clcc53z.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-3k-242-clcc53z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet

# Recommended By Lemo

## Accessories

Compatible cap	<a href="#">BFG.3K.100.NAS</a>
----------------	--------------------------------

## Tools

Die Tool	<a href="#">DPE.99.103.8K</a>
Extraction tool	<a href="#">DCC.91.CP1.LAG</a>
Spanner wrench	<a href="#">DCD.3E.ZZZ.PA150</a>

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-3k-242-clcc53z.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-3k-242-clcc53z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.