



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	2
Wire Size/AWG	14 - 10
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	10.10 - 10.50 mm
Size	3K
Suggested matching part	<a href="#">EGG.3K.302.CYM</a>
Series	K - Outdoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-3k-302-cycc11.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-3k-302-cycc11.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	2
Contact Termination Low voltage	Crimp
R (max)	3.1 mOhm
Insert configuration value	3K.302 - 2 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated current	35 A
Vtest (contact-contact)	3.2 kV (DC)
Vtest (contact-shell)	2.6 kV (DC)
Contact retention	75 N
Max. Conductor	4 mm <sup>2</sup> (AWG 10)
Min. Conductor	2.5 mm <sup>2</sup> (AWG 14)
Bucket Dia.	2.9 mm (0.114in)
Contact Dia.	3 mm (0.118in)
Wire Size/AWG	14 - 10
Gender	Standard

## Form & Material

Shell style / Model id	FG - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	65.25 g

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-3k-302-cycc11.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-3k-302-cycc11.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	10.10 - 10.50 mm

# Recommended By Lemo

## Accessories

Replacement contact	<a href="#">FGG.3B.580.ZZC</a>
Compatible cap	<a href="#">BFG.3K.100.NAS</a>

## Tools

Positionner	<a href="#">DCE.91.303.BVCM</a>
Extraction tool	<a href="#">DCC.30.35B.LAG</a>
Crimp tool	<a href="#">DPC.91.102.V</a>
Spanner wrench	<a href="#">DCD.3E.ZZZ.PA150</a>

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-3k-302-cycc11.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-3k-302-cycc11.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.