



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

Number of contacts Low Voltage	10
Number of contacts High Voltage	2
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	14.10 - 15.00 mm
Size	3K
Series	K - Outdoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-3k-7h0-cjck15.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-3k-7h0-cjck15.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	10
Contact Termination Low voltage	Crimp
Number of contacts High Voltage	2
Contact Termination High voltage	Crimp
Insert configuration value	3K.7H0 - 2 High V. 10 Low V.
Insulator	J: PEEK/PEEK
Rated current	2 A
Gender	Standard

## Form & Material

Shell style / Model id	FG - Straight plug with oversize cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	104.71 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr


[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/fgg-3k-7h0-cjck15.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-3k-7h0-cjck15.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	14.10 - 15.00 mm

Drawings



Dimensions

	M	L	B	S2	S1	A
mm.	65	85	22	19	19	19
in.	2.56	3.35	0.87	0.75	0.75	0.75

Recommended By Lemo

Accessories

Compatible cap	<a href="#">BFG.3K.100.NAS</a>
----------------	--------------------------------