



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|---------------------------------|
| Number of contacts Low Voltage | 11 |
| Wire Size/AWG | 30 - 22 |
| Plug | Plug - Straight |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 6.70 - 7.50 mm |
| Size | 3P |
| Suggested matching part | EGG.3P.310.PLNG |
| Series | REDEL P - Push-Pull |

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/fgg-3p-310-plyd75g.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---------------------------------|--|
| Contact Termination Low voltage | Crimp |
| Insert configuration value | 3P.310 - 10 Low Voltage + 1 Ground contact |
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Rated current | 5 A |
| Contact Type | Special |
| Contact Dia. | 0.9 |
| Number of contacts Low Voltage | 11 |
| Wire Size/AWG | 30 - 22 |

Form & Material

| | |
|------------------------|--|
| Shell style / Model id | FG - Straight plug with key and cable seal |
| Plug | Straight |
| Housing material | PSU (Polysulfone), gray |
| Locking system | Push-pull |
| Keying | User configurable, 1 of 11 key positions. Plug: male contacts, Receptacle: female contacts |
| Weight | 21.51 g |

Environment

| | |
|-----------------------------------|---|
| Technical domain | Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP61 |
| Endurance | >3000 mating cycles |
| Temperature range | -50°C / +150°C |
| F ret (max) | 200 N |
| F ret (min) | 100 N |
| Steam sterilization | Fully sterilizable (Steam, Gamma, ETO) following our protocols and tests in line with ISO 11134 and IEC 60601-1 standards. For more details on sterilization methods and cycles, please contact us. |



https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/fgg-3p-310-plyd75g.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

| | |
|------------------------------------|--|
| Cable termination protection | Standard back nut (no additional protection) |
| Fixation type | Cable collet |
| Jacket cable outside diameter [mm] | 6.70 - 7.50 mm |

Drawings



Dimensions

| | A | L |
|-----|------|------|
| mm. | 21.2 | 63 |
| in. | 0.83 | 2.48 |

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/fgg-3p-310-plyd75g.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.