



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	22
Wire Size/AWG	26 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	12.10 - 12.80 mm
Size	3T
Suggested matching part	EGG.3T.322.KYM
Series	T - Small Outdoor keyed

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgg-3t-322-kyck12.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	22
Contact Termination Low voltage	Crimp
R (max)	6.1 mOhm
Insert configuration value	T.322 - 22 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated current	5.5 A
Vtest (contact-contact)	2.4 kV (DC)
Vtest (contact-shell)	2 kV (DC)
Contact retention	22 N
Max. Conductor	0.34 mm ² (AWG 22)
Min. Conductor	0.14 mm ² (AWG 26)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	26 - 22
Gender	Standard

Form & Material

Shell style / Model id	FG - Straight plug with oversize cable collet
Plug	Straight
Housing material	Brass (black chrome) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Black

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgg-3t-322-kyck12.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Environment

Environmental sealing (IP rating)	IP68
Endurance	>3000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Resistance to vibration	15 g [10 Hz - 2000 Hz]
Shock Resistance	100 g [6 ms]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	12.10 - 12.80 mm

Drawings



Dimensions

	A	B	L	M	S1	S2	S3
mm.	18.8	23	87.7	72.7	16	20	20
in.	0.74	0.91	3.45	2.86	0.63	0.79	0.79

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgg-3t-322-kyck12.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Accessories	
Replacement contact	FGG.3B.555.ZZC
Compatible cap	BFG.3T.100.KAS
Tools	
Spanner	DCP.2T.110.TN
Positionner	DCE.91.073.BVC
Extraction tool	DCC.07.04B.LAG
Crimp tool	DPC.91.701.V