



Image for illustrative purpose only

## Summary

<a href="#">Request a quote</a>	
<a href="#">Catalog</a>	
Number of contacts Low Voltage	1
Size	5B
Series	B - Indoor keyed

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	1
Contact Termination Low voltage	PCB - Straight
Contact Dia.	0.7

## Form & Material

Shell style / Model id	FG - Male crimp contact for REDEL 1P series, standard barrel
Keying	No keying
Weight	0.13 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	No IP rating
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

# Recommended By Lemo

## Tools

Crimp tool	<a href="#">DPC.91.701.V</a>
------------	------------------------------

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-5b-555-zzd.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-5b-555-zzd.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.