



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Wire Size/AWG	30 - 22
Gender	Reverse Gender
Plug	Plug - Straight
Locking system	Push-pull
Size	4B
Suggested matching part	EGJ.4B.89E.CLA5
Series	B - Indoor keyed

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgj-4b-89e-clld28z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Insulator	L: PEEK (UL 94 / V-0/1.5)
Contact Dia.	0.9
Wire Size/AWG	30 - 22
Gender	Reverse Gender

Form & Material

Shell style / Model id	FG - Straight plug, cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	2 keys (alpha=37.5, plug: female contacts, receptacle: male contacts)
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	119.25 g

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgj-4b-89e-clld28z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation



Cable termination protection

For cable bend relief

Fixation type

Cable collet

Drawings



Dimensions

	A	L	M	S2	S1
mm.	25	71	53	20	21
in.	0.98	2.8	2.09	0.79	0.83

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgj-4b-89e-clld28z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.