



Image for illustrative purpose only

Summary

Request a quote	
Catalog	
Number of contacts Low Voltage	4
Wire Size/AWG	18 - 14
Gender	Reverse Gender
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	6.60 - 7.00 mm
Size	3T
Series	T - Small Outdoor keyed

Technical details

Electrical Configuration

Number of contacts Low Voltage	4
Contact Termination Low voltage	Crimp
R (max)	3.3 mOhm
Insert configuration value	T.304 - 4 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated current	17 A
Vtest (contact-contact)	3.4 kV (DC)
Vtest (contact-shell)	2.5 kV (DC)
Contact retention	65 N
Max. Conductor	1.5 mm ² (AWG 14)
Min. Conductor	1 mm ² (AWG 18)
Bucket Dia.	1.9 mm (0.075in)
Contact Dia.	2 mm (0.079in)
Wire Size/AWG	18 - 14
Gender	Reverse Gender

Form & Material

Shell style / Model id	FG - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	L: 2 keys (gamma=70, plug: female contacts, receptacle: male contacts)
Colour	Grey

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgl-3t-304-cypc70.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Environment

Environmental sealing (IP rating)	IP68
Endurance	>3000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Resistance to vibration	15 g [10 Hz - 2000 Hz]
Shock Resistance	100 g [6 ms]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	6.60 - 7.00 mm

Drawings



Dimensions

	A	L	M	S1	S2
mm.	18.8	64	49	16	14
in.	0.74	2.52	1.93	0.63	0.55

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgl-3t-304-cypc70.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Accessories	
Replacement contact	EGG.3B.676.ZZM
Compatible cap	BFG.3T.100.CAS
Tools	
Spanner	DCP.2T.110.TN
Positionner	DCE.91.203.BVCM
Extraction tool	DCC.20.25B.LAG
Crimp tool	DPC.91.101.A

Cables

Cable PartNumber	Material	Colour	Cable image
240750	PVC	Grey	