



## Summary

[Request a quote](#)

[Catalog](#)

[See video assembly instructions](#)

Number of contacts Low Voltage	2
Wire Size/AWG	24 - 20
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	3.80 - 9.00 mm
Size	0F
Matching parts	<a href="#">EGN.0F.302.XLM</a>
Series	F - Rugged Push-Pull

## Technical details

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/fgn-0f-302-xlc.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-0f-302-xlc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Contact Termination Low voltage	Crimp
R (max)	4.8 mOhm
Insert configuration value	0F.302 - 2 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	10 Amps
Vtest (contact-contact)	1450 V (AC), 2100 V (DC)
Vtest (contact-shell)	1200 V (AC), 1700 V (DC)
Contact retention	30 N
Contact Type	Crimp
Max. Conductor	0.5 mm <sup>2</sup> (AWG 20)
Min. Conductor	0.25 mm <sup>2</sup> (AWG 24)
Bucket Dia.	1.1 mm (0.043in)
Contact Dia.	0.9 mm (0.035in)
Number of contacts Low Voltage	2
Wire Size/AWG	24 - 20
Gender	Standard

## Form & Material

Shell style / Model id	FG - Straight plug
Plug	Straight
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Push-pull
Keying	3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	6.46 g

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/fgn-0f-302-xlc.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-0f-302-xlc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Motorsport, Security and Defence
Environmental protection (IP rating)	IP67
Minimal temperature	-15°C / +200°C
Climatical Category	15/200/21 (Aluminium shell)
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

## Cable fixation

Cable termination protection	Heatshrink
Fixation type	Cable collet
Jacket cable outside diameter [mm]	3.80 - 9.00 mm

# Recommended By Lemo

## Accessories

Replacement contact	<a href="#">FGG.0B.560.ZZC</a>
---------------------	--------------------------------























## Tools

Positionner	<a href="#">DCE.91.090.BVC</a>
Extraction tool	<a href="#">DCC.09.05B.LAG</a>
Crimp tool	<a href="#">DPC.91.701.V</a>

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/fgn-0f-302-xlc.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-0f-302-xlc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Cables

Cable PartNumber	Material	Colour	Cable image
CMN.02.T20.047PGZE		grey	
CMN.02.T20.047PNZE			
CMN.02.T20.048QGZE	TPR (medical)	Grey	
102080	PVC	Grey	
120184	PVC	Black	
120240	PVC	Black	
120250	PVC	Grey	
120500	PVC	Grey	
120501	PVC	Grey	
120751	PVC	Grey	
20140	PVC	Grey	
20140	PVC	Grey	
20142	PVC	Red	
20143	PVC	Green	
20144	PVC	Black	
20145	PVC	Yellow	
20146	PVC	Black	
20260	PVC	Black	
20264	PVC	Black	
20266	PVC	Violet	
220750	PVC	Grey	
2221	PVC	Black	
2280	PVC	Black	
4082	PVC	Grey	

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/fgn-0f-302-xlc.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-0f-302-xlc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.