



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	1
Wire Size/AWG	20 - 18
Jacket cable outside diameter [mm]	3.80 - 10.70 mm
Size	1F
Series	F - Rugged Push-Pull

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-1f-565-zzc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	1
Contact Termination Low voltage	Crimp
Contact Dia.	1.3
Wire Size/AWG	20 - 18

Form & Material

Shell style / Model id	FG - Male crimp contact for F series, standard barrel
Housing material	Gold plated [ISO 27874] brass
Keying	No keying
Weight	0.24 g


Environment

Technical domain	Motorsport, Security and Defence
Environmental sealing (IP rating)	No IP rating

Cable fixation

Cable termination protection	Heatshrink
Fixation type	Heatshrink
Jacket cable outside diameter [mm]	3.80 - 10.70 mm

Drawings



No keying

Dimensions

	A	C
mm.	1.3	1.4
in.	0.05	0.06

Recommended By Lemo

Tools

Crimp tool

[DPC.91.701.V](#)

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-1f-565-zzc.html

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.