



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

[See video assembly instructions](#)

|                                    |                                |
|------------------------------------|--------------------------------|
| Number of contacts Low Voltage     | 8                              |
| Wire Size/AWG                      | 24 - 20                        |
| Gender                             | Standard                       |
| Plug                               | Plug - Straight                |
| Locking system                     | Ratchet                        |
| Jacket cable outside diameter [mm] | 6.50 - 13.00 mm                |
| Size                               | 2M                             |
| Suggested matching part            | <a href="#">EGN.2M.308.XLM</a> |
| Series                             | M - Rugged Ratchet coupling    |

[https://www.lemo.com/int\\_en/solutions/optima/m-ratchet-coupling/fgn-2m-308-xlc.html](https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/fgn-2m-308-xlc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

|                                       |                               |
|---------------------------------------|-------------------------------|
| Contact Termination Low voltage       | Crimp                         |
| R (max)                               | 4.8 mOhm                      |
| Insert configuration value            | 2M.308 - 8 Low Voltage        |
| Insulator                             | L: PEEK                       |
| Rated current                         | 10 A                          |
| Test voltage (kV rms) Contact-contact | 1.95                          |
| Test voltage (kV rms) Contact-shell   | 1.1                           |
| Contact retention                     | 30 N                          |
| Contact Type                          | Crimp                         |
| Max. Conductor                        | 0.5 mm <sup>2</sup> (AWG 20)  |
| Min. Conductor                        | 0.25 mm <sup>2</sup> (AWG 24) |
| Bucket Dia.                           | 1.1 mm (0.043in)              |
| Contact Dia.                          | 0.9 mm (0.035in)              |
| Number of contacts Low Voltage        | 8                             |
| Wire Size/AWG                         | 24 - 20                       |
| Gender                                | Standard                      |

## Form & Material

|                        |   |
|------------------------|---|
| Shell style / Model id | FG - Straight plug with arctic grip   |
| Plug                   | Straight  |
| Housing material       | Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass |
| Locking system         | Ratchet   |
| Keying                 | N: 3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)                        |
| Colour                 | Grey  |
| Weight                 | 9.6 g   |

[https://www.lemo.com/int\\_en/solutions/optima/m-ratchet-coupling/fgn-2m-308-xlc.html](https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/fgn-2m-308-xlc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



## Environment

|                                   |  |
|-----------------------------------|--|
| Technical domain                  | Motorsport, Security and Defence, Transportation, Aerospace and UAV    |
| Environmental sealing (IP rating) | IP68   |
| Endurance                         | 3000 mating cycles   |
| Temperature range                 | -55°C / +200°C   |
| EMI Shielding EIA 364-66A         | >= 80 dB (1 GHz), >=70 dB (3 GHz), >= 58 dB (6 GHz), >= 40 dB (10 GHz) |
| Gunfire vibration                 | 25 Hz - 2000 Hz, 3 axis (Apache helicopter)                            |
| Humidity (max)                    | 21 days at 95%   |
| Lighting strike EIA 364-76        | 10K amps - 6 times   |
| Shock Resistance                  | 300 g [ 3 ms]  |
| Thermal shock                     | 5 cycles: -65°C to +150°C  |
| Vibration-Random                  | 37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]                        |
| Vibration-Sine                    | 30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]                                  |
| Salt Spray Corrosion              | max. 48 hr   |

## Cable fixation

|                                    |                 |
|------------------------------------|-----------------|
| Cable termination protection       | Heatshrink      |
| Fixation type                      | Cable collet    |
| Jacket cable outside diameter [mm] | 6.50 - 13.00 mm |

## Drawings



## Dimensions

|     | A    | B    | C    | D    | Ls   | Lr   | P    | X    |
|-----|------|------|------|------|------|------|------|------|
| mm. | 18.9 | 14   | 17.2 | 13   | 24.5 | 24.5 | 3.9  | 7.1  |
| in. | 0.74 | 0.55 | 0.68 | 0.51 | 0.96 | 0.96 | 0.15 | 0.28 |

[https://www.lemo.com/int\\_en/solutions/optima/m-ratchet-coupling/fgn-2m-308-xlc.html](https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/fgn-2m-308-xlc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

## Accessories

---

Replacement contact [FGN.0M.560.ZZC](#)

---

Compatible cap [BGF.2M.100.XAV](#)

## Tools

---

Positionner [DCE.91.090.5MVC](#)

---

Extraction tool [DCC.09.05B.LAG](#)

---

Crimp tool [DPC.91.701.V](#)

[https://www.lemo.com/int\\_en/solutions/optima/m-ratchet-coupling/fgn-2m-308-xlc.html](https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/fgn-2m-308-xlc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.