



Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.00 - 6.00 mm
Size	1S
Matching parts	ERA.1S.275.CTME61
Series	S - Indoor Stepped Insert

Technical details

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/fgz-1s-275-ctce61z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Electrical Configuration

Coax	1
Contact Termination Coax	Crimp
Insert configuration value	1S.275 - 1 Coax (75 Ohm)
Insulator	T: PTFE
Rated current	3 Amps
Impedance	75 Ohm
VSWR	Compliant to SMPTE 2082-1 norm. See catalogue for more information.
Vtest	1200 V (AC)
Contact Type	Coaxial 75 Ohm (Crimp)
Cable type	Cable type: A DRAKA ULTRA PRO 50 HD, BELDEN 4855R S
Bucket Dia.	0.75 mm (0.03in)
Contact Dia.	0.6 mm (0.02in)

Form & Material

Shell style / Model id	FGZ - Straight plug - design chocolate block, cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Weight	22.3 g

Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental protection (IP rating)	IP50
Minimal temperature	-55°C / +260°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Salt Spray Corrosion	>1000 hr

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/fgz-1s-275-ctce61z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Crimp
Jacket cable outside diameter [mm]	4.00 - 6.00 mm

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/fgz-1s-275-ctce61z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.