



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Fiber optic	2
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	6.60 - 7.50 mm
Size	SH

https://www.lemo.com/int_en/fhe-sh-03a-xlzt76n.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Fiber optic	2
Insert configuration value	SH.03A - 2 FO TYPE F2

Form & Material

Shell style / Model id	FHE - Straight plug (IP68)
Plug	Straight
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with male pin 1


Environment

Environmental sealing (IP rating)	IP68
Salt Spray Corrosion	max. 48 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	T type cable adapter
Jacket cable outside diameter [mm]	6.60 - 7.50 mm

Drawings



Dimensions

	A	L	M	N	S2
mm.	28.5	98.4	90	54	13
in.	1.12	3.87	3.54	2.13	0.51

https://www.lemo.com/int_en/fhe-sh-03a-xlzt76n.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.