

## Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Locking system	Push-pull
Jacket cable outside diameter [mm]	2.40 - 3.00 mm
Size	0A

## Technical details

### Electrical Configuration

Coax	1
Contact Termination Coax	Solder
Insert configuration value	0A.275 - 1 Coax (75 Ohm)
Contact Type	Coaxial 75 Ohm (Solder)
Bucket Dia.	0.65

[https://www.lemo.com/int\\_en/fls-0a-275-ctae31.html](https://www.lemo.com/int_en/fls-0a-275-ctae31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Form & Material

---

Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	11.41 g

---

## Environment

---

Environmental protection (IP rating)	IP50
Salt Spray Corrosion	>1000 hr

---

## Cable fixation

---

Cable termination protection	Standard back nut (no additional protection)
Jacket cable outside diameter [mm]	2.40 - 3.00 mm

---

# Recommended By Lemo

## Accessories

---






## Tools

---

[https://www.lemo.com/int\\_en/fls-0a-275-ctae31.html](https://www.lemo.com/int_en/fls-0a-275-ctae31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Cables

Cable PartNumber	Material	Colour	Cable image
17420	PVC	Black	
17450	COPOLYMER	Black	
18700	PTFE	White	
18800	PTFE	White	
31600	PTFE	Brown	
CCX.50.RG0.58AU14B	FEP	white	
CCX.50.RG1.74-U25N	PVC	Black	
CCX.50.RG1.74AU28N	PVC	Black	
CCX.50.RG1.74AU28N	PVC	Black	
CCX.50.RG1.74U25N	PVC	Black	
CCX.50.RG1.88AU24B	TFE	white	
CCX.50.RG1.88AU26B	PFA	White	
CCX.50.RG1.88AU26B	PTFE	White	
CCX.50.RG3.16BU26M	FEP	Brown	
CCX.50.RG3.16U28M	PTFE	Brown	
CCX.75.RG1.79BU26M	FEP	Brown	
CCX.75.RG1.87AU26B	PFA	White	
CCX.75.RG1.87AU27B	PTFE	White	

[https://www.lemo.com/int\\_en/fls-0a-275-ctae31.html](https://www.lemo.com/int_en/fls-0a-275-ctae31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.