

Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Locking system	Push-pull
Jacket cable outside diameter [mm]	3.20 - 3.90 mm
Size	0A

Technical details

Electrical Configuration

Coax	1
Contact Termination Coax	Solder
Insert configuration value	0A.275 - 1 Coax (75 Ohm)
Contact Type	Coaxial 75 Ohm (Solder)
Bucket Dia.	0.65

https://www.lemo.com/int_en/fls-0a-275-ctae40.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	11.41 g

Environment

Environmental protection (IP rating)	IP50
Salt Spray Corrosion	>1000 hr

Cable fixation



Cable termination protection	Standard back nut (no additional protection)
Jacket cable outside diameter [mm]	3.20 - 3.90 mm

Recommended By Lemo

Accessories

Tools

Cables

Cable PartNumber	Material	Colour	Cable image
18000	PTFE	Brown	
CCX.75.040.195327G	PVC	Grey	
CCX.95.RG1.80BU36M	PTFE	Brown	
CCX.95.RG1.95AU37B	PFA	White	

https://www.lemo.com/int_en/fls-0a-275-ctae40.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.