



## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	6
Wire Size/AWG	28 - 20
Gender	Standard
Plug	Plug - Straight
Locking system	Threaded
Jacket cable outside diameter [mm]	7.60 - 8.00 mm
Size	2W
Matching parts	<a href="#">EVG.2W.306.CLL</a>
Series	W - Underwater

## Technical details

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/fvg-2w-306-clac80.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-2w-306-clac80.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Contact Termination Low voltage	Solder
R (max)	3.6 mOhm
Insert configuration value	2W.306 - 6 Low Voltage
Rated current	12 Amps
Vtest (contact-contact)	1350 V (AC) 1900 V (DC)
Vtest (contact-shell)	1450 V (AC) 2100 V (DC)
Contact Type	Solder
Max. Solid Conductor	0.5 mm <sup>2</sup> (AWG 20)
Max. Stranded Conductor	0.5 mm <sup>2</sup> (AWG 20)
Bucket Dia.	1 mm (0.039in)
Contact Dia.	1.3 mm (0.051in)
Number of contacts Low Voltage	6
Wire Size/AWG	28 - 20
Gender	Standard

## Form & Material

Shell style / Model id	FV - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	1 key (alpha=0, Plug: male contacts, Receptacle: female contacts)
Weight	52.93 g

## Environment

Technical domain	Specialties and Other
Environmental protection (IP rating)	IP68
Minimal temperature	-20°C / +200°C
Climatical Category	20/200/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	30 bars
Salt Spray Corrosion	>1000 hr

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/fvg-2w-306-clac80.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-2w-306-clac80.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	7.60 - 8.00 mm

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/fvg-2w-306-clac80.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-2w-306-clac80.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.