



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	10
Wire Size/AWG	30 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Threaded
Jacket cable outside diameter [mm]	4.60 - 5.00 mm
Size	2W
Suggested matching part	<a href="#">EVG.2W.310.CLL</a>
Series	W - Underwater

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/fvg-2w-310-clac50.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-2w-310-clac50.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	10
Contact Termination Low voltage	Solder
R (max)	4.8 mOhm
Insert configuration value	2W.310 - 10 Low Voltage
Rated current	8 A
Vtest (contact-contact)	1450 V (AC) 2100 V (DC)
Vtest (contact-shell)	1300 V (AC) 1800 V (DC)
Max. Solid Conductor	0.34 mm <sup>2</sup> (AWG 22)
Max. Stranded Conductor	0.34 mm <sup>2</sup> (AWG 22)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.9 mm (0.035in)
Wire Size/AWG	30 - 22
Gender	Standard

## Form & Material

Shell style / Model id	FV - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	G: 1 key (alpha=0, Plug: male contacts, Receptacle: female contacts)
Colour	Grey
Weight	53.83 g

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/fvg-2w-310-clac50.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-2w-310-clac50.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Specialties and Other
Environmental sealing (IP rating)	IP68
Endurance	1000 mating cycles
Temperature range	-20°C / +200°C (max. temperature valid for short periods of use.)
Climatical Category	20/200/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	30 bars
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	4.60 - 5.00 mm

# Recommended By Lemo

## Accessories

Compatible cap	<a href="#">BFG.2W.100.NAZ</a>
----------------	--------------------------------

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/fvg-2w-310-clac50.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-2w-310-clac50.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.