



Image for illustrative purpose only

Summary

[Request a quote](#)

Number of contacts Low Voltage	8
Protocol	1000 Base-T4 (10Gb/s)
Wire Size/AWG	24 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Threaded
Jacket cable outside diameter [mm]	9.10 - 9.50 mm
Size	2W
Series	W - Underwater

https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-2w-514-cyck95.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Contact Termination Low voltage	Crimp
Insert configuration value	2W.514 - 8 High Speed, Low Voltage (CAT 6A)
Rated current	5 A
Number of contacts Low Voltage	8
Protocol	1000 Base-T4 (10Gb/s)
Wire Size/AWG	24 - 22
Gender	Standard

Form & Material

Shell style / Model id	FV - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	G: 1 key (alpha=0, Plug: male contacts, Receptacle: female contacts)
Colour	Grey
Weight	71.44 g

Environment

Technical domain	Specialties and Other
Environmental sealing (IP rating)	IP68
Endurance	1000 mating cycles
Temperature range	-20°C / +200°C
Climatical Category	20/200/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	30 bars
Salt Spray Corrosion	>1000 hr

https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-2w-514-cyck95.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	9.10 - 9.50 mm

Recommended By Lemo

Accessories

Replacement contact	FGG.2B.555.ZZC
Compatible cap	BFG.2W.100.NAZ

Tools

Positionner	DCE.91.072.BVC
Extraction tool	DCC.07.04B.LAG
Crimp tool	DPC.91.701.V

https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-2w-514-cyck95.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.