



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Gender	Standard
Plug	Plug - Straight
Locking system	Threaded
Jacket cable outside diameter [mm]	10.60 - 12.00 mm
Size	3W
Series	W - Underwater

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/fvg-3w-8h4-clak111.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-3w-8h4-clak111.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Rated current	2 A
Gender	Standard

## Form & Material

Shell style / Model id	FV_K - Straight plug, oversize cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	G: 1 key (alpha=0, Plug: male contacts, Receptacle: female contacts)
Colour	Grey
Weight	127.88 g

## Environment

Technical domain	Specialties and Other
Environmental sealing (IP rating)	IP68
Endurance	1000 mating cycles
Temperature range	-20°C / +200°C
Climatical Category	20/200/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	30 bars
Salt Spray Corrosion	>1000 hr



## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	10.60 - 12.00 mm

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/fvg-3w-8h4-clak111.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-3w-8h4-clak111.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Drawings



## Dimensions

	<b>A</b>	<b>B</b>	<b>L</b>	<b>M</b>	<b>N</b>	<b>S1</b>	<b>S2</b>	<b>S3</b>
mm.	27.8	22	80.5	67	16.5	26	19	19
in.	1.09	0.87	3.17	2.64	0.65	1.02	0.75	0.75

## Recommended By Lemo

### Accessories

Compatible cap

[BFG.3W.100.NAZ](#)

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/fvg-3w-8h4-clak111.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-3w-8h4-clak111.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.