



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	14
Wire Size/AWG	30 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	9.60 - 10.00 mm
Size	3N
Suggested matching part	<a href="#">EDY.3N.314.TLL</a>
Series	N - Nuclear Stainless Steel

[https://www.lemo.com/int\\_en/solutions/supreme/n-nuclear-stainless-steel/fzy-3n-314-tlay10.html](https://www.lemo.com/int_en/solutions/supreme/n-nuclear-stainless-steel/fzy-3n-314-tlay10.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Contact Termination Low voltage	Solder
R (max)	4.8 mOhm
Insert configuration value	3N.314 - 14 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	9 A
Contact Type	Solder
Max. Solid Conductor	0.34 mm <sup>2</sup> (AWG 22)
Max. Stranded Conductor	0.34 mm <sup>2</sup> (AWG 22)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.9 mm (0.035in)
Number of contacts Low Voltage	14
Wire Size/AWG	30 - 22
Gender	Standard

## Form & Material

Shell style / Model id	FZY - Straight plug for lever with positioning pin, cable clamp and smooth handling surface
Plug	Straight
Housing material	Stainless steel shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Push-Pull latch with additional lever. Male contacts
Colour	Grey
Weight	204.8 g

## Environment

Technical domain	Energy and Industrial, Specialties and Other
Environmental sealing (IP rating)	IP66


[https://www.lemo.com/int\\_en/solutions/supreme/n-nuclear-stainless-steel/fzy-3n-314-tlay10.html](https://www.lemo.com/int_en/solutions/supreme/n-nuclear-stainless-steel/fzy-3n-314-tlay10.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	9.60 - 10.00 mm

## Drawings



## Dimensions

	<b>A</b>	<b>B</b>	<b>L</b>	<b>M</b>	<b>N</b>	<b>P</b>	<b>S1</b>	<b>S2</b>
mm.	25	38	103	55	1	25	21	20
in.	0.98	1.5	4.06	2.17	0.04	0.98	0.83	0.79

[https://www.lemo.com/int\\_en/solutions/supreme/n-nuclear-stainless-steel/fzy-3n-314-tlay10.html](https://www.lemo.com/int_en/solutions/supreme/n-nuclear-stainless-steel/fzy-3n-314-tlay10.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.