



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Coax	1
Size	00
Series	00 - NIM-CAMAC

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/gba-00-250-fn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Coax	1
Rated current	4 A
OHM	50

Form & Material

Shell style / Model id	GBA - Locking washer
Housing material	Bronze (nickel plated [SAE AMS QQ N 290]) washer
Keying	Circular (can rotate)
Weight	0.15 g

Environment

Environmental sealing (IP rating)	No IP rating
F ret (min)	100 N

Drawings



Dimensions

	A	C	L
mm.	9.5	7.1	1
in.	0.37	0.28	0.04

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/gba-00-250-fn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.