



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|----------------------|
| Jacket cable outside diameter [mm] | 3.80 - 9.00 mm |
| Size | 0F |
| Series | F - Rugged Push-Pull |

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/gec-0f-240-rr.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Form & Material

| | |
|--------|-----------|
| Keying | No keying |
| Weight | 0.3 g |

Environment

| | |
|-----------------------------------|----------------------------------|
| Technical domain | Motorsport, Security and Defence |
| Environmental sealing (IP rating) | No IP rating |
| Temperature range in water steam | +140°C |

Cable fixation

| | |
|------------------------------------|----------------|
| Jacket cable outside diameter [mm] | 3.80 - 9.00 mm |
|------------------------------------|----------------|

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/gec-0f-240-rr.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.