



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

---

Jacket cable outside diameter [mm]	1.10 - 1.40 mm
------------------------------------	----------------

---

Size	00
------	----

[https://www.lemo.com/int\\_en/gma-00-012-dr.html](https://www.lemo.com/int_en/gma-00-012-dr.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Form & Material

Shell style / Model id	GMA - Bend relief Red
Housing material	Thermoplastic polyurethane
Keying	No keying
Colour	Red
Variant	Red
Weight	0.26 g

## Environment

Environmental sealing (IP rating)	No IP rating
-----------------------------------	--------------

## Cable fixation

Jacket cable outside diameter [mm]	1.10 - 1.40 mm
------------------------------------	----------------

[https://www.lemo.com/int\\_en/gma-00-012-dr.html](https://www.lemo.com/int_en/gma-00-012-dr.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.