



Summary

[Request a quote](#)

[Catalog](#)

Jacket cable outside diameter [mm]	4.50 - 4.90 mm
Size	1B
Series	B - Indoor keyed

Technical details

Form & Material

Shell style / Model id	GMA - Bend relief Blue
Housing material	Thermoplastic polyurethane
Keying	No keying
Variant	Blue
Weight	0.81 g

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-1b-045-da.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental protection (IP rating)	No IP rating
Minimal temperature	-40°C / +80°C

Cable fixation

Jacket cable outside diameter [mm]	4.50 - 4.90 mm
------------------------------------	----------------

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-1b-045-da.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.