



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Jacket cable outside diameter [mm]	4.50 - 4.90 mm
Size	1B
Series	B - Indoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/gma-1b-045-db.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-1b-045-db.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Form & Material

Shell style / Model id	GMA - Bend relief White
Housing material	Thermoplastic polyurethane
Keying	No keying
Colour	White
Variant	White
Weight	0.85 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	No IP rating
Temperature range	-40°C / +80°C

## Cable fixation

Jacket cable outside diameter [mm]	4.50 - 4.90 mm
------------------------------------	----------------

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/gma-1b-045-db.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-1b-045-db.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.