



Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|------------------|
| Jacket cable outside diameter [mm] | 5.00 - 5.50 mm |
| Size | 2B |
| Series | B - Indoor keyed |

Technical details

Form & Material

| | |
|------------------------|----------------------------|
| Shell style / Model id | GMA - Bend relief Grey |
| Housing material | Thermoplastic polyurethane |
| Keying | No keying |
| Variant | Gray |
| Weight | 1.66 g |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-2b-050-dg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

| | |
|--------------------------------------|--|
| Technical domain | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental protection (IP rating) | No IP rating |
| Minimal temperature | -40°C / +80°C |

Cable fixation

| | |
|------------------------------------|----------------|
| Jacket cable outside diameter [mm] | 5.00 - 5.50 mm |
|------------------------------------|----------------|

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-2b-050-dg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.