



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

---

[Catalog](#)

---

Size	2B
Series	B - Indoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/gma-2b-080-sn.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-2b-080-sn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details


## Form & Material

Shell style / Model id	GMA - Bend relief Black
Housing material	Santoprene thermoplastic
Keying	No keying
Colour	Black
Variant	Black
Weight	1.47 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	No IP rating
Temperature range	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

## Drawings



No keying

## Dimensions

	A	L
mm.	8.0	41
in.	0.31	1.61

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/gma-2b-080-sn.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-2b-080-sn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.