



## Summary

[Request a quote](#)

[Catalog](#)

Jacket cable outside diameter [mm]	8.00 - 8.90 mm
Size	3B
Series	B - Indoor keyed

## Technical details

### Form & Material

Shell style / Model id	GMA - Bend relief Black
Housing material	Thermoplastic polyurethane
Keying	No keying
Variant	Black
Weight	2.35 g

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/gma-3b-080-dn.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-3b-080-dn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

---

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental protection (IP rating)	No IP rating
Minimal temperature	-40°C / +80°C

---

## Cable fixation

---

Jacket cable outside diameter [mm]	8.00 - 8.90 mm
------------------------------------	----------------

---

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/gma-3b-080-dn.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-3b-080-dn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.