



Image for illustrative purpose only

Summary

[Request a quote](#)

unipole multipole

Size

4A

https://www.lemo.com/int_en/gmp-4a-080-145nn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Form & Material

Keying	No keying
--------	-----------

Weight	58.22 g
--------	---------

Environment

Environmental sealing (IP rating)	No IP rating
-----------------------------------	--------------

Climatic Category	55/175/21
-------------------	-----------

Humidity (max)	<=95% [at 60 deg C /140 F]
----------------	----------------------------

Drawings

No keying

https://www.lemo.com/int_en/gmp-4a-080-145nn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.