



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Jacket cable outside diameter [mm]	1.40 - 2.20 mm
------------------------------------	----------------

Size	00
------	----

https://www.lemo.com/int_en/gsc-00-290-cd22.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Insert configuration value	0.29 - no contacts
----------------------------	--------------------

Form & Material

Shell style / Model id	GSC - Lead through with cable collet
------------------------	--------------------------------------

Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
------------------	---

Keying	No keying
--------	-----------

Colour	Grey
--------	------

Weight	2.55 g
--------	--------

Environment

Environmental sealing (IP rating)	No IP rating
-----------------------------------	--------------

Salt Spray Corrosion	>1000 hr
----------------------	----------

Cable fixation

Jacket cable outside diameter [mm]	1.40 - 2.20 mm
------------------------------------	----------------

https://www.lemo.com/int_en/gsc-00-290-cd22.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.