



Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	1
Wire Size/AWG	16 - 8
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	2.60 - 22.60 mm
Size	3E
Series	E - Outdoor Stepped Insert

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/hgp-3e-160-cllp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Contact Termination Low voltage	Solder
Insert configuration value	3E.160 - 1 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	65 A
Vtest	1700 V (AC), 2400 V (DC)
Contact Type	Solder
Contact Dia.	6
Number of contacts Low Voltage	1
Wire Size/AWG	16 - 8

Form & Material

Shell style / Model id	HGP - Fixed receptacle, nut fixing, watertight or vacuum-tight
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Circular, female
Variant	Watertight unmated (connector to device)
Weight	77.29 g

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/hgp-3e-160-cllp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-20°C / +80°C
Climatical Category	20/80/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Pressure	30 bars
Salt Spray Corrosion	>1000 hr

Cable fixation

Jacket cable outside diameter [mm]	2.60 - 22.60 mm
------------------------------------	-----------------

Drawings



Dimensions

	B	e	E	L	M	S1	S3	A
mm.	34	M24x1.0	15.5	39.5	6	22.5	30	31
in.	1.34		0.61	1.56	0.24	0.89	1.18	1.22

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/hgp-3e-160-cllp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.