



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	6
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Size	1B
Suggested matching part	<a href="#">FGG.1B.306.CLAD42</a>
Series	B - Indoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/hhg-1b-306-cnnp.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/hhg-1b-306-cnnp.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	6
Contact Termination Low voltage	PCB - Straight
R (max)	6.1 mOhm
Insert configuration value	1B.306 - 6 Low Voltage
Insulator	N: PBT (discontinued)
Rated current	7 A
Vtest (contact-contact)	1050 V (AC), 1490 V (DC)
Vtest (contact-shell)	1200 V (AC), 1700 V (DC)
Contact Dia.	0.7 mm (0.028in)
Gender	Standard

## Form & Material

Shell style / Model id	HH - Fixed receptacle, nut fixing, watertight or vacuum-tight (watertight when mated)
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Watertight unmated (connector to device)
Weight	12.88 g


[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/hhg-1b-306-cnnp.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/hhg-1b-306-cnnp.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-20°C / +100°C
Climatical Category	20/80/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Pressure	60 bars
Salt Spray Corrosion	>1000 hr

## Drawings



## Dimensions

	<b>A</b>	<b>B</b>	<b>e</b>	<b>E</b>	<b>L</b>	<b>M</b>	<b>S1</b>	<b>S3</b>
mm.	18	16	M12x1.0	7	29.7	5.2	10.5	14
in.	0.71	0.63		0.28	1.17	0.2	0.41	0.55

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/hhg-1b-306-cnnp.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/hhg-1b-306-cnnp.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.