



Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	10
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Threaded
Size	2W
Matching parts	FVG.2W.310.CLAC50Z
Series	W - Underwater

Technical details

Electrical Configuration

Contact Termination Low voltage	PCB - Straight
R (max)	4.8 mOhm
Insert configuration value	2W.310 - 10 Low Voltage
Rated current	8 Amps
Contact Type	Print (straight)
Contact Dia.	0.9 mm (0.035in)
Number of contacts Low Voltage	10
Gender	Standard



https://www.lemo.com/int_en/solutions/supreme/w-underwater/hvg-2w-310-clnpv.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

Shell style / Model id	HV - Fixed socket, nut fixing, vacuumtight
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	1 key (alpha=0, Plug: male contacts, Receptacle: female contacts)
Variant	Watertight / Vacuum-tested unmated (connector to device)
Weight	28.31 g

Drawings



Dimensions

	A	B	e	e1	E	L	N	S1	S2	S3
mm.	22.5	21.8	M16x1.0	M20x1.0	12	35.8	9	14.5	18.5	19
in.	0.89	0.86			0.47	1.41	0.35	0.57	0.73	0.75

https://www.lemo.com/int_en/solutions/supreme/w-underwater/hvg-2w-310-clnpv.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.