



Summary

[Request a quote](#)

[Catalog](#)

Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	MP
Series	REDEL MP - Modular Inner Push-Pull

https://www.lemo.com/int_en/solutions/redel/redel-mp/mkn-v04-gezg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Insulator	L: PEEK (UL 94 / V-0/1.5)
Gender	Standard

Form & Material

Shell style / Model id	MK - Socket, key (N) or keys (P, S and T), with two nuts (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Proprietary sulfone, grey
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Variant	Grey front nut
Weight	13.4 g

Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	>2000 mating cycles
Temperature range	-50°C / +170°C

https://www.lemo.com/int_en/solutions/redel/redel-mp/mkn-v04-gezg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.