



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|---------------------|--|
| Gender | Standard |
| Socket / Receptacle | Socket / Receptacle - Fixed Panel Rear Mounted |
| Locking system | Push-pull |
| Size | MP |
| Series | REDEL MP - Modular Inner Push-Pull |

Technical details

Electrical Configuration

| | |
|-----------|---------------------------|
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Gender | Standard |

Form & Material

| | |
|------------------------|--|
| Shell style / Model id | MK - Socket, key (N) or keys (P, S and T), with two nuts (back panel mounting) |
| Socket / Receptacle | Fixed Panel Rear Mounted |
| Housing material | Proprietary sulfone, grey |
| Locking system | Push-pull |
| Keying | 3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts) |
| Colour | Grey |
| Variant | Grey front nut |
| Weight | 13.4 g |

Environment

| | |
|-----------------------------------|--|
| Technical domain | Energy and Industrial, Medical, Test and Measurement |
| Environmental sealing (IP rating) | IP50 |
| Endurance | >2000 mating cycles |
| Temperature range | -50°C / +170°C |

https://www.lemo.com/int_en/solutions/redel/redel-mp/mkn-v04-gezg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.