



Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	6
Wire Size/AWG	32 - 24
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 6.50 mm
Size	1P
Matching parts	PLG.M0.6NL.LN
Series	REDEL P - Push-Pull

Technical details

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-6nl-ac65nz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Electrical Configuration

Contact Termination Low voltage	Solder
R (max)	6.5 mOhm
Insert configuration value	1P.M06 - 6 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	6 Amps
Test voltage (kV rms) Contact-contact	1.05
Contact Type	Solder
Max. Solid Conductor	0.14 mm ² (AWG 26)
Max. Stranded Conductor	0.14 mm ² (AWG 26)
Air clearance	0.85 mm
Creepage distance	0.85 mm
Bucket Dia.	0.6 mm (0.024in)
Contact Dia.	0.7 mm (0.0275in)
Number of contacts Low Voltage	6
Wire Size/AWG	32 - 24
Gender	Standard

Form & Material

Shell style / Model id	PA - Straight plug with cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	PSU (Polysulfone), black
Locking system	Push-pull
Keying	1 key (alpha=0, Plug: male contact, Receptacle: female contact)
Variant	Black collet nut for bend relief
Weight	4.33 g

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-6nl-ac65nz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental protection (IP rating)	IP50
Minimal temperature	-50°C / +150°C
F ret (max)	150 N
F ret (min)	50 N
Steam sterilization	> 100 times (with potting on rear connection)

Cable fixation


Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 6.50 mm

Recommended By Lemo

Accessories

Tools

Cables

Cable PartNumber	Material	Colour	Cable image
12080	PVC	Grey	
260250	PVC	Grey	

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-6nl-ac65nz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.